## CK9480-000 | FIST-RSKG-16



FIST Gel Sealing Kit for round splice closure port, sealing 16 cables with diameter up to 3 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

#### **Product Classification**

Regional Availability EMEA

Product Type Gel sealing kit
Product Series FIST-GC02

General Specifications

**Application** For use with FIST-GC02 Fiber closures

Cable Capacity, maximum 16
Color Black

**Dimensions** 

Agency

Single Cable Diameter, maximum 3 mm | 0.118 in

#### Packaging and Weights

Included Cable termination brackets | Dummy plugs | Multi-out gel seal

Packaging quantity

### Regulatory Compliance/Certifications

Classification

Agency	Olassification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





# CK9480-000 | FIST-RSKG-16

