

E46515-000 | VCKT-200-24-INT



VCKT Vault Copper Closure, unpressurized, heat shrink, 740 mm joint length, 24 MDF cable outlets

- Vault closure system for the distribution of telecommunication cables in telephone exchanges
- Flexibility arises from selective use of break-out ports up to 3/9/12 or 24 MDF cables
- Vertical installation with re-entry option of the splice area for testing and measuring

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Unpressurized heat shrink closure
Product Series	VCKT

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Branch-off Clip	To be ordered separately
Cable Capacity, maximum	25
Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Color	Black
Splice Protection Type	Metal canister

Dimensions

Length	950 mm 37.402 in
Single Cable Diameter, maximum	36 mm 1.417 in
Single Cable Diameter, minimum	12 mm 0.472 in
Splice Bundle Diameter, maximum	196 mm 7.717 in
Sheath Opening, nominal	740 mm 29.134 in

Environmental Specifications

E46515-000 | VCKT-200-24-INT

Environmental Space Above ground | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity wire | Underclips

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

