# FDP-G4PS22144



CMT Fiber Termination/Splice Panel, 144, FC/UPC, pre-terminated with pigtails, singlemode, 13RU, 19 in, putty white

#### OBSOLETE

This product was discontinued on: March 1, 2018

# Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	CMT

## General Specifications

Functionality	Patching   Splicing
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Interface, front	FC/UPC
Patch Cord Entry Location	Front, left side   Front, right side
Rack Type	EIA 19 in   EIA 23 in
Rack Units	13
Total Ports, quantity	144
Dimensions	

Height	577.85 mm   22.75 in
Width	482.6 mm   19 in
Depth	304.8 mm   12 in

### Material Specifications

#### Finish

Powder coated

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 20, 2023



# FDP-G4PS22144

Material Type

Steel

## **Optical Specifications**

Fiber Mode

Singlemode

## Packaging and Weights

IncludedMounting hardwarePackaging quantity1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 20, 2023

