

# TFP-12APLC8

---

TFP Fiber Optic Adapter Pack, Singlemode, 6 SC UPC duplex adapters, blue

## Product Classification

<b>Regional Availability</b>	Asia   Latin America   North America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber adapter pack
<b>Product Series</b>	TFP

## General Specifications

<b>Application</b>	For use with TFP panels
<b>Adapter Color</b>	Blue
<b>Adapters, quantity, front</b>	6
<b>Body Style</b>	Duplex   Left orientation
<b>Color, front</b>	Black
<b>Interface</b>	SC/UPC
<b>Total Ports, quantity, front</b>	12

## Dimensions

<b>Height</b>	33.53 mm   1.32 in
<b>Width</b>	176.02 mm   6.93 in

## Ordering Tree

# TFP-12APLC8

TFP - X X AP X X X X X X

## Number of Fiber Ports

12	12 fiber ports: 6 LC adapters; 6 SC duplex adapters; 12 ST adapters
24	24 fiber ports: 12 LC adapters

## Pack Orientation

L	angle left
R	angle right

## Adapter Style

Multimode Connectors	
C3	SC duplex (beige)
C4	SC duplex (aqua)
Q1	LC (beige)
Q2	LC (aqua)
T1	ST®
Singlemode Connectors	
C8	SC UPC duplex (blue)
A2	SC APC duplex (green)
Q5	LC UPC (blue)
T2	ST UPC

## Pigtail Length

Leave Blank	Adapters only
3	3 meter pigtails

## Pigtail Type

Leave Blank	Adapters only
B	Singlemode stranded
E	Multimode stranded

## Fiber Size

Leave Blank	Adapters only
B	OM1 - 62.5/125 Multimode
D	OM3 - 50/125 LOMMF 300m
S	Singlemode

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** 0 °C to +70 °C (+32 °F to +158 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant/Exempted

# TFP-12APLC8

---

