2055108



Fiber Optic Patch Cord, Duplex, OM3, SC/UPC to SC/UPC, LSZH, Aqua

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | India

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Series 205

General Specifications

Connector A, quantity 2

Color, boot A Blue

Color, connector A Beige

Connector B, quantity 2

Color, boot B Blue

Color, connector B Beige

Interface, Connector A SC/UPC

Interface, Connector B SC/UPC

Jacket Color Aqua

Polarity Pairs, flipped

Total Fibers, quantity 2

Dimensions


Cable Assembly Length Range (m) 1 – 30

Diameter Over Jacket 1.8 mm | 0.071 in

Ordering Tree



2055108



Optical Specifications

Fiber Mode Multimode

Fiber Type OM3, LazrSPEED®

Insertion Loss, maximum0.15 dBReturn Loss, minimum35 dB

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Low Smoke Zero Halogen (LSZH)

Qualification Standards | IEC 60332-1 | IEC 60332-3 | IEC 60754 | IEC 61034

Packaging and Weights

Packaging quantity 1

