2105032

Base Product



Fiber Optic Patch Cord, Singlemode, LC/UPC to SC/UPC duplex, 1.8 mm LSZH & OFNR, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Middle East/Africa

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Series 210

General Specifications

Connector A, quantity 2

Color, boot A Blue

Color, connector A Blue

Connector B, quantity 2

Color, boot B Blue

Color, connector B Blue

Interface, Connector A LC/UPC

Interface, Connector B SC/UPC

Jacket Color Yellow

Polarity Pairs, flipped

Total Fibers, quantity 2

Dimensions


Cable Assembly Length Range (m) 1 - 100

Diameter Over Jacket 1.8 mm | 0.071 in

Ordering Tree



2105032



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

 Insertion Loss, maximum
 0.25 dB

 Return Loss, minimum
 50 dB

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Dual Rated LSZH/Riser

Packaging and Weights

Packaging quantity 1