

# C240-NRQMR

---

## Base Product



CNT-240 CNT® Jumper with interface types N Male Right Angle and QMA Male Right Angle, variable length

## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-240

## General Specifications

<b>Body Style, Connector A</b>	Right angle
<b>Body Style, Connector B</b>	Right angle
<b>Cable Family</b>	CNT-240
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	QMA Male
<b>Orientation</b>	0°
<b>Specification Sheet Revision Level</b>	A
<b>Variable Length</b>	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

## Dimensions

<b>Length</b>	0 m   0 ft
<b>Nominal Size</b>	0.240 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

## Jumper Assembly Sample Label

# C240-NRQMR



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

- 240BPNR-CR – Type N Male Right Angle for CNT-240 and CNT-240-Flex braided cable
- 240PQMR-C-CR – QMA Male Right Angle for CNT-240 braided cable
- 240PQMR-CA – QMA Male Right Angle for CNT-240 braided cable, for jumpers only not for sale
- CNT-240 – CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket
- CNT-240-SFR – CNT-240-SFR, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket