## FFWLCSC42

#### **Base Product**



Singlemode LC/UPC to SC/UPC, Fiber Patch Cord, 1.6 mm Duplex, Low Smoke Zero Halogen (LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber patch cord, duplex

Product Brand SYSTIMAX InstaPATCH® 360

Product Series FFW

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

### General Specifications

Connector A, quantity 2

Color, boot A Blue

Color, connector A Blue

Connector B, quantity 2

Color, boot B Blue

Color, connector B Blue

Interface, Connector A LC/UPC

Interface, Connector B SC/UPC

Jacket Color Yellow

**Polarity** Method B

Total Fibers, quantity 2

Dimensions

Cable Assembly Length Range (m) 1 - 999


**COMMSCOPE®** 

## FFWLCSC42

Cable Assembly Length Range (ft) 1 - 999

**Diameter Over Jacket** 1.6 mm | 0.063 in

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.652.D | G.657.A1, TeraSPEED®

### **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Environmental Space** Dual Rated LSZH/Riser

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





# FFWLCSC42

#### Included Products

760021675 – Fiber Indoor Cable, TeraSPEED® 1.6mm Low Smoke Zero Halogen Riser, 2-fiber Zipcord, N-002-ZC-8W-F16YL/E Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Eca Flame Rating

860637435 – LC/UPC Connector, Singlemode, Blue, Short Boot

860648965 – SC/UPC Connector, Singlemode, Blue

