CGANB | IP06-06PUTP-01S-1100L

Base Product



InstaPATCH® Cu GigaSPEED XL® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to 1100 module, 6 links

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Copper trunk cable assembly

Product Brand GigaSPEED XL® | InstaPATCH® Cu

General Specifications

ANSI/TIA Category 6

Cable Type U/UTP (unshielded)

Conductor Type Solid

Interface, Connector A Information outlet

Interface Feature, connector A Single row | Standard density

Interface, Connector B1100 moduleInterface Feature, connector BStandard

Link Count 6

Wiring T568B

Dimensions

Cable Assembly Length Range (m)2-90Cable Assembly Length Range (ft)7-295


Electrical Specifications

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree



CGANB | IP06-06PUTP-01S-1100L



Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 °F to +140 °F)}$

Environmental Space Plenum
Flammability Rating UL 94 V-0

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

2071E-4/23 – GigaSPEED XL® 2071E ETL Verified Category 6 U/UTP Cable, plenum, 4 pair

count

MGS400 – GigaSPEED XL® M-Series Modular Jack, RJ45, Cat6 Unshielded

