

# FJZMPMPAL

## Base Product



OM3 MPO (Unpinned) to MPO (Unpinned), InstaPATCH® 360 Pre-terminated Trunk Cable, 96-Fiber, Low Smoke Zero Halogen

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America  |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber trunk cable assembly  |
| <b>Product Brand</b>         | SYSTIMAX InstaPATCH® 360  |
| <b>Ordering Note</b>         | For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration   Not available in the United States or Canada |

## General Specifications

|                                     |                   |
|-------------------------------------|-------------------|
| <b>Color, boot A</b>                | Black             |
| <b>Color, connector A</b>           | Aqua              |
| <b>Color, boot B</b>                | Black             |
| <b>Color, connector B</b>           | Aqua              |
| <b>Construction Type</b>            | Stranded          |
| <b>Furcation Color</b>              | Aqua              |
| <b>Interface, Connector A</b>       | MPO-12/UPC Female |
| <b>Interface, Connector B</b>       | MPO-12/UPC Female |
| <b>Jacket Color</b>                 | Aqua              |
| <b>Polarity</b>                     | Method B (LL)     |
| <b>Fibers per Subunit, quantity</b> | 12                |
| <b>Total Fibers, quantity</b>       | 96                |

## Dimensions

|                        |       |
|------------------------|-------|
| <b>Breakout Length</b> | 33 in |
|------------------------|-------|



# FJZMPMPAL

---

## Included Products

- 760050450  
N-096-MP-5L-F12AQ/D – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber multi-unit with 12 fiber subunits, Gel-free, Multimode OM3, Feet jacket marking, Aqua jacket color, Dca flame rating
- 860647054 – MPO12, LOW LOSS, FEMALE, OM3/4, AQUA, 3mm