


UDGLCUC21

Base Product



Ultra Low Loss (ULL) Singlemode LC/UPC to Unconnectorized, 1.6 mm Simplex Fiber Pigtail, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand Europe Latin America Middle East /Africa North America
Portfolio	CommScope®
Product Type	Fiber pigtail, jacketed
Product Brand	SYSTIMAX ULL
Product Series	UDG
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications


Color, boot A	Blue
Color, connector A	Blue
Interface, Connector A	LC/UPC
Jacket Color	Yellow
Total Fibers, quantity	1

Dimensions

Cable Assembly Length Range (m)	1 – 61
Cable Assembly Length Range (ft)	2 – 200
Diameter Over Jacket	1.6 mm 0.063 in

Ordering Tree

UDGLCUC21



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

- 760238067 – 1.6 mm Plenum Simplex Cable
- P-001-SP-8G-F16YL
- 860637435 – LC/UPC Connector, Singlemode, Blue, Short Boot