UDVLULUK2

Base Product



Ultra Low Loss OM5, LC/UPC Uniboot to LC/UPC Uniboot, 1.5 mm Duplex Fiber Patch Cord, Plenum

- Patch cords using Uniboot technology combine, modularity, flexibility with easy insertion and removal from connectivity
- Uniboot connectors feature an adjustable polarity via a manual and independent rotation of each single connector body without exposing the fibers
- Uniboot technology features a push-pull mechanism operated by squeezing the connector boot

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Brand SYSTIMAX ULL

Product Series UDV

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

 Color, connector A
 Beige

 Color, connector B
 Beige

 Interface, Connector A
 LC/UPC

 Interface Feature, connector A
 Uniboot

 Interface, Connector B
 LC/UPC

 Interface Feature, connector B
 Uniboot

Total Fibers, quantity 2

Dimensions

Jacket Color

Cable Assembly Length Range (m) 1 - 999

Cable Assembly Length Range (ft) 1 - 999


Diameter Over Jacket 1.5 mm | 0.059 in

COMMSCOPE®

Lime green

UDVLULUK2

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$ | 4.40 lb @ 90 $^{\circ}$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

 Insertion Loss, maximum
 0.15 dB

 Return Loss, minimum
 35 dB

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSAbove maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemROHSCompliant/ExemptedUK-ROHSCompliant/Exempted



Included Products

760251284 – Fiber indoor cable, LazrSPEED® Plenum Light Duty Interconnect Cordage, 2 fiber, Multimode P-002-DU-5G-M15LM/AY/LTS OM5, Meters jacket marking, Lime green jacket color

Page 2 of 3

UDVLULUK2

