

# UJVMPMXCD

## Base Product



Ultra Low Loss ULL LazrSPEED® 550 OM5 MPO(Unpinned) to MPO (Pinned) Pre-terminated Trunk Cable, MPO12, 12-Fiber, LSZH, 12 fiber PmP 2.0 mm Dca

## Product Classification

|                              |                                                                                                                                                                                                          |
|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   Europe   Latin America   Middle East/Africa   North America                                                                                                               |
| <b>Portfolio</b>             | CommScope®                                                                                                                                                                                               |
| <b>Product Type</b>          | Fiber trunk cable assembly                                                                                                                                                                               |
| <b>Product Brand</b>         | SYSTIMAX ULL                                                                                                                                                                                             |
| <b>Ordering Note</b>         | For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration |

## General Specifications

|                                     |                         |
|-------------------------------------|-------------------------|
| <b>Color, boot A</b>                | Black                   |
| <b>Color, connector A</b>           | Black                   |
| <b>Color, boot B</b>                | Black                   |
| <b>Color, connector B</b>           | Black                   |
| <b>Construction Type</b>            | Stranded                |
| <b>Furcation Color</b>              | Lime green              |
| <b>Interface, Connector A</b>       | MPO-12/UPC Female       |
| <b>Interface, Connector B</b>       | MPO-12/UPC Male         |
| <b>Jacket Color</b>                 | Lime green              |
| <b>Polarity</b>                     | Method B Enhanced (ULL) |
| <b>Fibers per Subunit, quantity</b> | 12                      |
| <b>Total Fibers, quantity</b>       | 12                      |

## Dimensions

|                                         |          |
|-----------------------------------------|----------|
| <b>Breakout Length</b>                  | 33 in    |
| <b>Cable Assembly Length Range (m)</b>  | 3 – 999  |
| <b>Cable Assembly Length Range (ft)</b> | 10 – 999 |

## Ordering Tree



## Optical Specifications

|                   |                 |
|-------------------|-----------------|
| <b>Fiber Mode</b> | Multimode       |
| <b>Fiber Type</b> | OM5, LazrSPEED® |

## Environmental Specifications

|                                                     |                                      |
|-----------------------------------------------------|--------------------------------------|
| <b>Operating Temperature</b>                        | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Dca                                  |
| <b>Environmental Space</b>                          | Dual Rated LSZH/Riser   Indoor       |

# UJVMPMXCD

---

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                                                                 |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| ANATEL        | Compliant                                                                                                                      |
| CHINA-ROHS    | Above maximum concentration value                                                                                              |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system                                                 |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted                                                                                                             |
| UK-ROHS       | Compliant/Exempted                                                                                                             |



## Included Products

|                                      |   |                                                                                                                                                                                              |
|--------------------------------------|---|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 760244155<br>N-012-MP-5G-F12LM/20T/D | - | Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk with 2.0mm Subunits, 12 fiber, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color, Dca Flame rating |
| 860659008                            | - | MPO12, ULL, MALE, OM5, LIME, 2MM                                                                                                                                                             |
| 860659014                            | - | MPO12, ULL, FEMALE, OM5, LIME, 2MM                                                                                                                                                           |