A3GMPMPCL

Base Product



Ultra Low Loss ULL TeraSPEED® MPO(Unpinned) to MPO(Unpinned) Pre-terminated Trunk Cable, MPO12, 96-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca, Method A

Product Classification

Regional Availability Europe | Middle East/Africa

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

 Color, boot A
 Black

 Color, connector A
 Green

 Color, boot B
 Black

 Color, connector B
 Green

 Construction Type
 Stranded

 Furcation Color
 Yellow

 Interface, Connector A
 MPO-12/APC Female

 Interface, Connector B
 MPO-12/APC Female

Jacket ColorYellowPolarityMethod A

Fibers per Subunit, quantity 12

Total Fibers, quantity 96


Dimensions

Breakout Length33 inCable Assembly Length Range (m)3 - 999Cable Assembly Length Range (ft)10 - 999

COMMSC PE°

A3GMPMPCL

Ordering Tree



Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

COMMSCOPE®

A3GMPMPCL

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

