

# F1-UMMU-8

---

FSJ1-50A Jumper with interface types UHF Male and UHF Male, 2.44 m



## Product Classification

**Product Type** SureFlex® standard

**Product Series** FSJ1-50A

## General Specifications

**Body Style, Connector A** Straight

**Body Style, Connector B** Straight

**Interface, Connector A** UHF Male

**Interface, Connector B** UHF Male

**Specification Sheet Revision Level** A

## Dimensions

**Length** 2.44 m | 8.005 ft

**Nominal Size** 1/4 in

## Electrical Specifications

**DTF, Connector A** -10 dB

**DTF, Connector B** -10 dB

## Jumper Assembly Sample Label

# F1-UMMU-8



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

- |            |   |  |
|------------|---|--|
| 35422-33   | - | Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket  |
| 35422-75   | - | Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket            |
| F1MU       | - | Mini UHF Male for 1/4 in FSJ1-50A cable  |
| FSJ1-50A   | - | FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket   |
| FSJ1RK-50A | - | FSJ1-50A, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a dO a1 Compliant |