

# L2-PTMTM-20M-HF

---

LDF2-50 SureFlex® Jumper with interface types TNC Male and TNC Male, 20M



## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	LDF2-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	TNC Male
<b>Interface, Connector B</b>	TNC Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	20 m   65.617 ft
<b>Nominal Size</b>	3/8 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
1000–11000 MHz	1.93	10

## Jumper Assembly Sample Label

# L2-PTMTM-20M-HF



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

- 35422-23 – Heat Treated LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket
- L2TTM-PL – TNC Male Positive Lock for 3/8 in LDF2-50 cable
- LDF2-50 – LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket