

L4A-PDMDM-15

LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male



Product Classification

| | |
|-----------------------|--------------------|
| Product Type | SureFlex® standard |
| Product Series | LDF4-50A |

General Specifications

| | |
|---|---------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 7-16 DIN Male |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 4.572 m 15 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|-------------------------|--------|
| DTF, Connector A | -32 dB |
| DTF, Connector B | -32 dB |

Jumper Assembly Sample Label

L4A-PDMDM-15



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

LDF4-50A

- LDF4-50A, HELIAX[®] Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket (Halogen free jacketing non-fire-retardant)