

F4-DMDM-1M2-D

D-CLASS HELIAX® 1/2" ureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1.2 m



Product Classification

Product Type	SureFlex® D-CLASS, dynamic PIM
Product Series	RSJ4-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Length	1.2 m 3.937 ft
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Dynamic	-116 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB

Logo Image

F4-DMDM-1M2-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.065	30.04
1700-2200 MHz	1.065	30.04
2200-2700 MHz	1.106	25.96
3400-3800 MHz	1.222	20.01

Jumper Assembly Sample Label

Batch Manufacturing Date (two digit year and week)

Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMSCOPE® Andrew Solutions™

F4-DMDM-2M-D — Part Number

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710

Product of UNITED STATES 12US220001242 — Serial Number



F4-DMDM-1M2-D

Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

