

# F4-HMDR-5M-D

---



D-CLASS HELIAX® 1/2" SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Right Angle, 5 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

<b>Product Type</b>	SureFlex® D-CLASS, dynamic PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	RSJ4-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Right angle
<b>Interface, Connector A</b>	4.3-10 Male
<b>Interface, Connector B</b>	7-16 DIN Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	5 m   16.404 ft
<b>Nominal Size</b>	1/2 in

## Logo Image

# F4-HMDR-5M-D



## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-116 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037
<b>DTF, Connector A</b>	-34 dB
<b>DTF, Connector B</b>	-32 dB

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>698–960 MHz</b>	1.083	27.99
<b>1700–2200 MHz</b>	1.083	27.99
<b>2200–2700 MHz</b>	1.135	23.98
<b>3400–3800 MHz</b>	1.222	20.01

## Jumper Assembly Sample Label

# F4-HMDR-5M-D



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

