

# F4S-HMDR-5M-P



RSJ4-50 SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Right Angle Male, 5 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

|                       |                               |
|-----------------------|-------------------------------|
| <b>Product Type</b>   | SureFlex® Premium, static PIM |
| <b>Product Brand</b>  | HELIAX®   SureFlex®           |
| <b>Product Series</b> | RSJ4-50                       |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Right angle   |
| <b>Interface, Connector A</b>             | 4.3-10 Male   |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | A             |

## Dimensions

|                     |                 |
|---------------------|-----------------|
| <b>Length</b>       | 5 m   16.404 ft |
| <b>Nominal Size</b> | 1/2 in          |

## Electrical Specifications

|   |                      |
|---|----------------------|
| <b>3rd Order IMD Static</b>             | -116 dBm             |
| <b>3rd Order IMD Static Test Method</b> | Two +43 dBm carriers |
| <b>DTF, Connector A</b>                 | 34 dB                |
| <b>DTF, Connector B</b>                 | 34 dB                |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz    | 1.083 | 27.99            |
| 1700–2200 MHz  | 1.083 | 27.99            |
| 2200–2700 MHz  | 1.135 | 23.98            |

# F4S-HMDR-5M-P

## Jumper Assembly Sample Label



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

### Classification

|               |  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |



## Included Products

|         |   |
|---------|---|
| RSJ4-50 | - RSJ4-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket |
|---------|---|