


L4P43A-PNMDR-2M



Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	LDF4-50A

General Specifications

Attachment, Connector B	Field attachment
Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male

Dimensions

Length	2 m 6.562 ft
Nominal Size	1/2 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
710–806 MHz	1.2	20.83
806–960 MHz	1.15	23.13
1700–2180 MHz	1.15	23.13
2535–2655 MHz	1.2	20.83

Jumper Assembly Sample Label

L4P43A-PNMDR-2M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- LDF4-50A – LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket Halogen free jacketing non-fire-retardant (General propose cable for outdoor use only)