



Fiber Optic Pigtail, Single fiber white color, OM4, SC to Stub, 0.9 mm diameter, 1.5 m

Product Classification

Regional Availability	EMEA
Product Type	Fiber pigtail, jacketed
Product Series	OCP

General Specifications

Connector A, quantity	1
Color, boot A	Aqua
Color, connector A	Beige
Interface, Connector A	SC/UPC
Jacket Color	White
Total Fibers, quantity	1

Dimensions

Cord Length	1.5 m 4.921 ft
Diameter Over Jacket	0.9 mm 0.035 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

EH0108-007 | OCP-S5-15DGSEN-XX-AP

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

