



Fiber Optic Patch Cord, Multi-fiber, Singlemode, 4 fibers, SC/UPC to LC/UPC, yellow, 40 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution cable assembly
Product Series	FPM

General Specifications

Connector A, quantity	4
Color, boot A	Blue
Color, connector A	Blue
Connector B, quantity	4
Color, boot B	Blue
Color, connector B	Blue
Construction Type	Stranded
Interface, Connector A	LC/UPC
Interface, Connector B	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	4

Dimensions

Breakout Length, connector A	635 mm 25 in
Breakout Length, connector B	990.6 mm 39 in
Cord Length	40 m 131.234 ft

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.3 dB
Insertion Loss, maximum, connector B	0.2 dB

Return Loss, minimum, connector A	55 dB
Return Loss, minimum, connector B	55 dB

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

