

PTS1A-HFHF-2M8-P

PTS1-50-HRL SureFlex® Jumper with interface types 4.3-10 Female and 4.3-10 Female, 2.8M



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	PTS1-50-HRL

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Female
Interface, Connector B	4.3-10 Female
Specification Sheet Revision Level	A

Dimensions

Length	2.8 m 9.186 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD Dynamic	-113 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–960 MHz	1.135	23.98
1700–2700 MHz	1.135	23.98

Jumper Assembly Sample Label

PTS1A-HFHF-2M8-P



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition