



RJ45 Patch Cord, category 6, U/UTP, with security key, white, 2 m

- Both ends have a security key plug mechanism
- Prevents unauthorized disconnection
- Can be used for secure connections (e.g. server lines)

OBSOLETE

This product was discontinued on: December 31, 2018

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug with security key
Interface, Connector B	RJ45 plug with security key
Jacket Color	White
Pairs, quantity	4

Dimensions

Cord Length	2 m 6.562 ft
Diameter Over Jacket	5.58 mm 0.22 in
Compatible Conductor Gauge, stranded	24 AWG

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
------------------------------	-------------------------------------

2134201-2

Packaging and Weights

Included	Security key (2)
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

- 1871456-2 – RJ45 Security Key Plug kit with reserved number