


# F4A-PNMDR-3M

---



## Product Classification

<b>Product Type</b>	SureFlex® standard
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	RSJ4-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Right angle
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	7-16 DIN Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	3 m   9.843 ft
<b>Nominal Size</b>	1/2 in

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR, typical</b>	<b>Return Loss, typical (dB)</b>
<b>0–3000 MHz</b>	1.106	25.96
<b>2.2–2.7 GHz</b>	1.083	27.99

## Jumper Assembly Sample Label

# F4A-PNMDR-3M

---



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system