

F1P43A-PNMNM-3M

FSJ1P-50A SureFlex® Jumper with interface types N Male and N Male,
3 m



Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	3 m 9.843 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
695–806 MHz	1.15	23.13
806–960 MHz	1.13	24.29
1427–1535 MHz	1.13	24.29
1700–2300 MHz	1.15	23.13
2535–2655 MHz	1.25	19.08
3400–3800 MHz	1.25	19.08

Jumper Assembly Sample Label

F1P43A-PNMNM-3M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

