

F4-HMDM-4-D

D-CLASS HELIAX® 1/2" SureFlex® Jumper with interface types 4.3-10



Male and 7-16 DIN Male, 4 ft

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

| | |
|-----------------------|--------------------------------|
| Product Type | SureFlex® D-CLASS, dynamic PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|---------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|--------------------|
| Length | 1.219 m 3.999 ft |
| Nominal Size | 1/2 in |

Logo Image

F4-HMDM-4-D



Electrical Specifications

| | |
|--|------------------------------------|
| 3rd Order IMD Dynamic | -116 dBm |
| 3rd Order IMD Dynamic Test Method | Two +43 dBm carriers per IEC 62037 |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|-----------------------|-------------|-------------------------|
| 698–960 MHz | 1.065 | 30.04 |
| 1700–2200 MHz | 1.065 | 30.04 |
| 2200–2700 MHz | 1.106 | 25.96 |
| 3400–3800 MHz | 1.222 | 20.01 |

Jumper Assembly Sample Label

F4-HMDM-4-D



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |