



RJ45 Patch Cord, category 5e, PVC stranded, with security key, gray, 3 m

OBSOLETE

This product was discontinued on: December 31, 2018

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	5e
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug with security key
Interface, Connector B	RJ45 plug with security key
Jacket Color	Gray
Pairs, quantity	4

Dimensions

Cord Length	3 m 9.843 ft
Diameter Over Jacket	4.9 mm 0.193 in
Compatible Conductor Gauge, stranded	24 AWG

Material Specifications

Conductor Material	Bare copper
---------------------------	-------------

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Non-plenum
Flammability Rating	CM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

