



Sigma-Link™ Universal Connectivity Platform Q-Fit Cable Assembly, STP, class EA, H to J, 40 m

- Sigma-Link is a pre-terminated factory-tested copper system for networking infrastructures and guarantees a 100% throughput performance
- Sigma-Link cable assemblies are offered in Housing-to-Housing, Housing-to-Jacks, Housing-to-Plugs and Housing to stub tail configurations
- Ranging from Category 6 to Category 7A, Sigma-Link supports up to 10GbE (10 Gigabit Ethernet) transmission and beyond
- Housing-to-Housing version features integrated Plastic Optical Fiber (POF) for easy tracing of far end

OBSOLETE

This product was discontinued on: September 1, 2016

Replaced By:

4-2153473-0

Sigma-Link™ Universal Connectivity Platform Q-Fit Cable Assembly, STP, class FA, H to J, POF, 40 m

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America
Portfolio	NETCONNECT®
Product Type	Copper trunk cable assembly
Product Brand	Sigma-Link™
Product Series	Sigma-Link UCP

General Specifications

ANSI/TIA Category	6A
Cable Type	S/FTP (shielded)
Conductor Type	Solid
Interface, Connector A	Information outlet
Interface Feature, connector A	Single row Standard density
Interface, Connector B	RJ45 jack
Interface Feature, connector B	Standard
Jacket Color	White
Link Count	6

4-2153151-0

Transmission Standards ISO/IEC 11801 Class EA

Dimensions

Cord Length 40 m | 131.234 ft

Material Specifications

Conductor Material Bare copper

Environmental Specifications

Environmental Space Low Smoke Fire Retardant Zero Halogen (LSFRZH)

Packaging and Weights

Packaging quantity 1