

imVision Controller X



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Controller unit
Product Brand	iPatch®

General Specifications

Color	Cool gray
--------------	-----------

Dimensions

Height	81.28 mm 3.2 in
Width	19 mm 0.748 in

Electrical Specifications

Input Voltage	100–240 Vac
Output Current at Voltage, continuous	2.08 A @ 12 Vdc
Power Frequency	50–60 Hz

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate Steel
----------------------	---

Environmental Specifications

Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	CE RCM UL

760237876 | imV-CNTRL-X

Packaging and Weights

Included	16 in panel bus jumper 7 ft patch cord Forty-four position bus panel Power supply, 2.08A @ 12 Vdc output, 100-240 Vac 50-60 Hz input
Packaging quantity	1
Weight, net	1.288 kg 2.84 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

