7643288-01 | SR 8/POI w/o guiderails



ION® Active Intelligent Point of Interface Subrack for ION-U Applications

Product Classification

Product Type Point of interface subrack

Product Brand ION®

General Specifications

General Alarm Integrated into management system

Interface Slots Available, quantity

Mounting Rack

Note Detailed Product Specifications are available. Please contact your

local CommScope representative.

Rack Type EIA 19 in

Slots Available, quantity 8

Dimensions

 Height
 177 mm | 6.969 in

 Width
 483 mm | 19.016 in

 Depth
 462 mm | 18.189 in

Electrical Specifications

Electrical Safety Standard EN 60950 **Power Consumption** 276 W

Voltage Range +10 to +14 Vdc

Environmental Specifications

Operating Temperature +5 °C to +50 °C (+41 °F to +122 °F)

COMMSCSPE®

7643288-01 | SR 8/POI w/o guiderails

Storage Temperature -25 °C to +70 °C (-13 °F to +158 °F)

Relative Humidity 46%-94%

Mean Time Between Failures (MTBF) at Temperature 213,000 h @ 25 °C

Packaging and Weights

 Height, packed
 570 mm | 22.441 in

 Width, packed
 305 mm | 12.008 in

 Depth, packed
 620 mm | 24.409 in

 Weight, gross
 11.6 kg | 25.574 lb

 Weight, net
 8 kg | 17.637 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

