

HN-10-SP



Head Frame - 1710 - 2170MHz Antennas with TMA Enclosure

OBSOLETE

This product was discontinued on: May 31, 2016

Product Classification

Product Type Head frame

General Specifications

Application Outdoor

Dimensions

Height 2000 mm | 78.74 in

Diameter, at zero degrees panning 345 mm | 13.583 in

Antenna Panning Capability ±25°

Weight, net 68 kg | 149.914 lb

Electrical Specifications

Lightning Protection Chassis ground

Mechanical Specifications

Wind Loading @ Velocity, maximum 600.0 N @ 160 km/h (134.9 lbf @ 160 km/h)

Wind Speed, maximum 200 km/h | 124.274 mph

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency **Classification**

HN-10-SP

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

