

Tel-Splice Connector, 3-wire, gel filled, translucent, 500 tube



OBSOLETE

This product was discontinued on: August 1, 2016

Replaced By:

CK1830-001
TEL-SPLICE II RF

Tel-Splice II Connector, 3-wire, gel filled, red

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Splice
Product Series	Tel-Splice

General Specifications

Color	Translucent
Connector Sealant	Gel filled

Dimensions

Compatible Insulated Conductor Diameter, maximum	2.03 mm 0.08 in
Compatible Conductor Gauge, solid	26-19 AWG

Material Specifications

Contact Plating Material	Tin
---------------------------------	-----

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Space	Outdoor

552678-2

Packaging and Weights

Packaging quantity	500
Packaging Type	Tube

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

