



HGS620 M-Series Adapter, Red (25 ea/pkg)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Adapter
Ordering Note	Minimum order quantity, 20 packs

General Specifications

Color	Red
Integrated Dust Cover Type	None

Dimensions

Height	17.53 mm 0.69 in
Width	18.54 mm 0.73 in
Depth	9.14 mm 0.36 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	25
---------------------------	----

Regulatory Compliance/Certifications

760154260 | HGS-A-MS-RD-25

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

