

# FD3-AB096J00AKBP3



Enhanced Mini FDH 3000 Fiber Distribution Hub, 96-fiber shell, 96 fibers loaded, SC/APC, distribution patch, feeder stub, No splitter loaded

## Alternative products available:

FD3-AB096J00AKBP3-US Enhanced Mini FDH 3000 Fiber Distribution Hub, 96-fiber shell, 96 fibers loaded, SC/APC, distribution patch, feeder stub, No splitter loaded, Build America Buy America (BABA)

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Dielectric - Ribbon
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	1
<b>Distribution Ports, quantity</b>	96
<b>Fibers per Distribution Cable, quantity</b>	96
<b>Fibers per Feeder Cable, quantity</b>	36
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pole   Wall
<b>Split Ratio</b>	Symmetrical
<b>Splitter Slots, quantity</b>	8
<b>Splitter Type</b>	1 x 32

## Dimensions

<b>Height</b>	584.2 mm   23 in
<b>Width</b>	330.2 mm   13 in

# FD3-AB096J00AKBP3

---

<b>Depth</b>	203.2 mm   8 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Mini

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Environmental Specifications

<b>Environmental Space</b>	Aerial
<b>Qualification Standards</b>	Telcordia GR-3123-CORE   Telcordia GR-3125-CORE

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

