



Vertical Cable Management Kit, 10in X 84in (254mm X 2134mm) Single Sided, With Door, Silver

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America
Portfolio CommScope®
Product Type Vertical cable management

General Specifications


Configuration Type Single-sided
Color Silver
Door, quantity 1

Dimensions

Height 2,133.6 mm | 84 in
Width 254 mm | 10 in
Depth 279.4 mm | 11 in

Trough Capacity

Ordered Installation - 40%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	492	492	397	397	248	248
8 in	671	671	541	541	338	338
10 in	850	850	685	685	429	429
12 in	1029	1029	829	829	518	518
Randomized Installation - 20%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	246	246	198	198	124	124
8 in	335	335	270	270	169	169
10 in	425	425	343	343	214	214
12 in	514	514	415	415	259	259



Cat.6A: 169
Cat.6: 270
Cat.5E: 335

Cat.6A: 169
Cat.6: 270
Cat.5E: 335

Top View of VCM
Example for 8" VCM Capacity (Randomized Installation - 20%)

Material Specifications

760244789 | VCM-SS-84-10

Finish Powder-coated, smooth

Material Type Metal

Environmental Specifications

Safety Standard UL | cUL

Packaging and Weights

Included Four 1/2-20 hex nuts | Four 1/2-20 x 1 in hex head bolts | Four flat washers | Instruction sheet | Two spools

Packaging quantity 1

Packaging Type Assembled

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

