

760244803 | VCM-DS-96-6B



Vertical Cable Management Kit, 6in X 96in (152mm X 2438mm) Double Sided, With Doors, Black

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America
Portfolio CommScope®
Product Type Vertical cable management

General Specifications

Configuration Type Double-sided
Color Black
Door, quantity 2

Dimensions

Height 2,438.4 mm | 96 in
Width 152.4 mm | 6 in
Depth 558.8 mm | 22 in

Trough Capacity

Ordered Installation - 40%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	492	492	397	397	248	248
8 in	671	671	541	541	338	338
10 in	850	850	685	685	429	429
12 in	1029	1029	829	829	518	518
Randomized Installation - 20%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	246	246	198	198	124	124
8 in	335	335	270	270	169	169
10 in	425	425	343	343	214	214
12 in	514	514	415	415	259	259

Top View of VCM

Example for 8" VCM Capacity (Randomized Installation - 20%)

Material Specifications

760244803 | VCM-DS-96-6B

Finish	Powder-coated, smooth
Material Type	Metal

Environmental Specifications

Safety Standard	UL cUL
------------------------	----------

Packaging and Weights

Included	Four 1/2-20 hex nuts Four 1/2-20 x 1 in hex head bolts Four flat washers Instruction sheet
Packaging quantity	1
Packaging Type	Assembled

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

