

WP-TH12-B



Wood Pole Top Hat, 12 ft 6 in face, 7 in to 14 in wood poles

Product Classification

Product Type Wood pole mount

General Specifications

Mounting Wood pole, 177.8–355.6 mm (7–14 in) OD

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Height 355.6 mm | 14 in

Face Width 3.81 m | 12.5 ft

Width 3810 mm | 150 in

Length 914.4 mm | 36 in

Mounting Diameter, maximum 355.6 mm | 14 in

Mounting Diameter, minimum 177.8 mm | 7 in

Pipe Outer Diameter 60.96 mm | 2.4 in

Stand-off Distance 914.4 mm | 36 in

Mounting Circumference, maximum 353.06 mm | 13.9 in

Mounting Circumference, minimum 175.26 mm | 6.9 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Platform | Ring mount

WP-TH12-B

Packaging quantity 1
Weight, net 771.016 kg | 1,699.8 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code