

FGS-HNTS-F-1/2-LP



FiberGuide® Low-Profile Top Support C-Bracket Kit, 1/2in for 4x12in System

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Bracket

Dimensions

Height	203.2 mm 8 in
Width	38.1 mm 1.5 in
Length	381 mm 15 in
Thread Size	1/2 in
System Dimensions	102 mm x 305 mm (4 in x 12 in)

Ordering Tree

FGS-HNTS-F-1/2-LP

FGS - - - - - - -

For Section Size

9	<input type="text" value="empty"/>	4 x 4 in, 4 x 6 in
	<input type="text" value="F"/>	4 x 12 in

For Threaded Rod Size

10	<input type="text" value="1/2"/>	1/2 in
	<input type="text" value="1/2-LP"/>	1/2 in, low profile
	<input type="text" value="12MM"/>	12 mm
	<input type="text" value="12MM-LP"/>	12 mm, low profile
	<input type="text" value="14MM"/>	14 mm
	<input type="text" value="14MM-LP"/>	14 mm, low profile
	<input type="text" value="16MM"/>	16 mm
	<input type="text" value="16MM-LP"/>	16 mm, low profile
	<input type="text" value="5/8"/>	5/8 in
	<input type="text" value="5/8-LP"/>	5/8 in, low profile

11	<input type="text" value="A"/>	Adjustable
----	--------------------------------	------------

Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware

Packaging quantity 1

Weight, net 3.615 kg | 7.97 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

