

FGS-HTHR-5/8-72



FiberGuide® Threaded Rod, 5/8in Diameter, 72in Length

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Threaded rod |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|---------------------|------------|
| Color | Silver |
| Orientation | Horizontal |
| Section Type | Mounting |

Dimensions

| | |
|--------------------------|--|
| Length | mm 72 in |
| Rod Length | 1,828.8 mm 72 in |
| Thread Size | 5/8 in |
| System Dimensions | 102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 51 mm x 152 mm (2 in x 6 in) |

Ordering Tree

FGS-HTHR-5/8-72

FGS - HTHR - $\overset{9}{\boxed{5/8}}$ - $\overset{10}{\boxed{72}}$

Rod Diameter

| | | |
|---|-------|--------|
| 9 | 1/2 | 1/2 in |
| | 5/8 | 5/8 in |
| | 12 MM | 12 mm |
| | 14 MM | 14 mm |
| | 16 MM | 16 mm |

Rod Length

| | | |
|----|-------|--------|
| 10 | 12 | 12 in |
| | 30 | 30 in |
| | 48 | 48 in |
| | 72 | 72 in |
| | 30CM | 30 cm |
| | 75CM | 75 cm |
| | 180CM | 180 cm |

* Rod diameter and length needs to be both metric or imperial sized

Packaging and Weights

Weight, net 1.216 kg | 2.681 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

