

FPM-OE/O-P030M

Fiber Optic Pigtail, Multi-fiber, Singlemode, 6 fibers, SC/APC to Stub, yellow, 30 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber pigtail, multi-fiber
Product Series	FPM

General Specifications

Color, boot A	Green
Color, connector A	Green
Connector A, quantity	6
Construction Type	Stranded
Interface, Connector A	SC/APC
Jacket Color	Yellow
Total Fibers, quantity	6

Dimensions

Cord Length	30 m 98.425 ft
--------------------	------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.35 dB
Return Loss, minimum, connector A	65 dB

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

FPM-0E/O-P030M

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

