

# IFC-7/02080-NGF

---

Intra Facility Fiber Cable, OS2, SC/UPC- stub, 48F, 80 m, NGF breakout 96-, 144-position

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber distribution cable assembly
<b>Product Series</b>	IFC

## General Specifications

<b>Color, boot A</b>	Blue
<b>Color, connector A</b>	Blue
<b>Connector A, quantity</b>	48
<b>Connector B, quantity</b>	0
<b>Construction Type</b>	Stranded
<b>Interface, Connector A</b>	SC/UPC
<b>Interface, Connector B</b>	Unterminated
<b>Jacket Color</b>	Yellow
<b>Total Fibers, quantity</b>	48

## Dimensions

<b>Cord Length</b>	80 m   262.467 ft
--------------------	-------------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2
<b>Insertion Loss, maximum, connector A</b>	0.2 dB
<b>Return Loss, minimum, connector A</b>	55 dB

## Environmental Specifications

<b>Environmental Space</b>	Riser
----------------------------	-------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

# IFC-7/02080-NGF

---

## Regulatory Compliance/Certifications

**Agency**

CHINA-ROHS

REACH-SVHC

ROHS

**Classification**

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

