

IFC-7/7VPO28-PPV

Fiber Optic Intra Facility Fiber Cable, OS2, SC/UPC to SC/UPC, yellow, 28 m

Product Classification

| | |
|------------------------------|-----------------------------------|
| Regional Availability | Latin America North America |
| Product Type | Fiber distribution cable assembly |
| Product Series | IFC |

General Specifications

| | |
|-------------------------------|--------|
| Color, boot A | Blue |
| Color, boot B | Blue |
| Color, connector A | Blue |
| Color, connector B | Blue |
| Connector A, quantity | 72 |
| Connector B, quantity | 72 |
| Interface, Connector A | SC/UPC |
| Interface, Connector B | SC/UPC |
| Jacket Color | Yellow |
| Total Fibers, quantity | 72 |

Dimensions

| | |
|--------------------|------------------|
| Cord Length | 28 m 91.864 ft |
|--------------------|------------------|

Optical Specifications

| | |
|---|------------|
| Fiber Mode | Singlemode |
| Fiber Type | OS2 |
| Insertion Loss, maximum, connector A | 0.2 dB |
| Insertion Loss, maximum, connector B | 0.2 dB |
| Return Loss, minimum, connector A | 57 dB |
| Return Loss, minimum, connector B | 57 dB |

Environmental Specifications

| | |
|----------------------------|-------|
| Environmental Space | Riser |
|----------------------------|-------|

IFC-7/7VP028-PPV

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |

