

760245548 | ODF-SPLCAB-24



UMSC (Universal Mounted Splice Cabinet) with up to 6912 fiber splices capacity (Rollable ribbon cables), exit up, gray, splice trays are not included

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Universal Mounted Splice Cabinet
Product Series	Flex Frame

General Specifications

Access	Front
Cable Entry Location	Top
Cable Exit Location	Top
Color	Gray
Growth Configuration	Unloaded
Mounting	Back to Back Rack, EIA 19 in Rack, EIA 23 in Wall
Splice Trays Included, quantity	0
Splicing Capacity Note	Up to 6912 Rollable Ribbon Splices
Splicing Capacity, maximum	6912

Dimensions

Height	1,747.3 mm 68.791 in
Width	443 mm 17.441 in
Depth	287.9 mm 11.335 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760245548 | ODF-SPLCAB-24

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

