

TFAH-EU26/26-14



ION®-B Series High Power Remote Unit MIMO for LTE 2600

OBSOLETE

Product Classification

Product Type	Remote unit
Product Brand	ION®-B

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	High

Electrical Specifications

Impedance	50 ohm
License Band	LTE 2600
Voltage Range	85 to 265 Vac

Electrical Specifications, Rx (Uplink)

Operating Frequency Band	2500 – 2570 MHz
---------------------------------	-----------------

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	2620 – 2690 MHz
---------------------------------	-----------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

TFAH-EU26/26-14

UK-ROHS

Compliant/Exempted



Included Products

TPSN1/28-150 - Power Supply Adapter ION®-B Series Remote Units, 150 W

TPSN1/28-150



Power Supply Adapter ION®-B Series Remote Units, 150 W

Product Classification

Product Type	Power adapters
Product Brand	ION®-B

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
-------------	--

Dimension Drawing

Electrical Specifications

Output Power, maximum	150 W
------------------------------	-------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

