

UA-3C



PIM free, Angle member attachment. Includes torque stop set bolt to ensure proper attachment force. Two 3/4" holes for Snap-in style hangers

- Includes torque stop set bolt to ensure proper attachment force

Product Classification

Product Type	Adapter
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Angle adapter
Color	Black
Mounting	3/4 in through hole Angle member
Patent Number	For patents see: www.cs-pat.com

Dimensions

Height	44.958 mm 1.77 in
Outside Width	49.022 mm 1.93 in
Inside Length	25.4 mm 1 in
Outside Length	42.672 mm 1.68 in
Compatible Diameter, maximum	11.113 mm 0.438 in
Compatible Diameter, minimum	3.175 mm 0.125 in
Material Thickness	3.175 mm 0.125 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Installation Torque, maximum	4 ft lb 5.423 N-m
Installation Torque, minimum	3 ft lb 4.067 N-m
Maximum Loading	Triple stack, 1/2 in cable

Environmental Specifications

UA-3C

Operating Temperature	-20 °C to +85 °C (-4 °F to +185 °F)
UV Resistance, minimum with no degradation	≥1000 hours

Packaging and Weights

Height, packed	25 cm 9.843 in
Width, packed	14 cm 5.512 in
Length, packed	12 cm 4.724 in
Packaging quantity	10
Weight, gross	0.5 kg 1.102 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

