
				3			2 REVISIONS	\$			
			REV.	ZC	ONE		DESCRIPTIO			BY	DATE
			Α				INITIAL RELEA	\SE		JTS	03/28/0
			В			REVERSED	HARDWARE FOR F	PROPER ASSEM	MBLY	ACG	09/29/0
4 5	6 7										
4 5		PART NO			Г)FS(~RIP ⁻	ΙΟΝ		OTY		WFI G HT
4 5	6 7 ITEM	PART NO.	NAI NAI	FDII IAA		DESCRIPT O DISH (I)APTFR	QTY.		WEIGHT 4 77 I BS
4 5	ITEM 1	M60SA			60° T0) H2IC C	ROUND) A		2	4	4.77 LBS
1 5	ITEM 1 2	M60SA MCF		X 11.5	60° T0 5'' X .5'	o dish (i ' straig	ROUND) A[HT BAR AD/	APTOR	2 2	4	4.77 LBS 3.08 LBS
1 5	1 2 3	M60SA MCF SC-P10		X 11.5	60° T0 5'' X .5' SMALL	O DISH (I ' STRAIG DISH CL	ROUND) AE HT BAR AD, AMP HALF	APTOR	2 2 2	4	4.77 LBS 3.08 LBS 1.20 LBS
5	ITEM 1 2 3 4	M60SA MCF SC-P10 12-04-FTB		X 11.5 S 1/2" x	60° T(5" X .5" 5MALL 4" FU	O DISH (I ' STRAIG DISH CL LL THREA	ROUND) AE HT BAR ADA AMP HALF AD GALV. B	APTOR SOLT	2 2 2 4	(4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS
1 5	1 2 3 4 5	M60SA MCF SC-P10 12-04-FTB GN04A		X 11.5 S 1/2" x 1,	60° T(5" X .5' 5MALL (4" FU /2" GA	O DISH (I ' STRAIG DISH CL LL THREA LLV HEX	ROUND) AE HT BAR ADA AMP HALF AD GALV. B NUT (A325)	APTOR SOLT	2 2 2 4 4	(4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS
1 5	ITEM 1 2 3 4 5 6	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04		X 11.5 S 1/2" x 1,	60° T(5" X .5" 5MALL (4" FU /2" GA /2" GA	O DISH (I ' STRAIG DISH CL LL THREA ALV HEX ALV LOC	ROUND) AE HT BAR AD, AMP HALF AD GALV. B NUT (A325) CK WASHER	APTOR SOLT	2 2 2 4 4		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS
5	1 2 3 4 5 6 7	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A		X 11.5 S 1/2" x 1, 1 1/2"	60° T(5" X .5' 5MALL (4" FU /2" GA /2" GALV	O DISH (I ' STRAIG DISH CL LL THREA LV HEX ALV LOC ' FLAT W	ROUND) AE HT BAR AD, AMP HALF AD GALV. B NUT (A325) CK WASHER ASHER (A32	APTOR OLT 25)	2 2 2 4 4 4 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS
5	ITEM 1 2 3 4 5 6 7 8	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8		X 11.5 S 1/2" x 1, 1/2" 5/8"	60° T0 5" X .5' 5MALL 4" FU /2" GA /2" GALV ' X 8" 0	O DISH (I ' STRAIG DISH CL LL THREA LV HEX ALV LOC ' FLAT W GALV TH	ROUND) AE HT BAR ADA AMP HALF AD GALV. B NUT (A325) EK WASHER ASHER (A32 READED RO	APTOR SOLT 25) DD	2 2 2 4 4 4 8 4		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS
4 5	1 2 3 4 5 6 7 8 9	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A		X 11.5 S 1/2" x 1, 1 1/2" 5/8"	60° T(5" X .5' 5MALL (4" FU /2" GA /2" GA GALV ' X 8" (D DISH (I STRAIG DISH CL LL THREA LV HEX ALV LOC FLAT W GALV TH LV HEX	ROUND) AE HT BAR AD, AMP HALF AD GALV. B NUT (A325) CK WASHER ASHER (A32 READED RO NUT (A325)	APTOR OLT 25) DD	2 2 2 4 4 4 8 4 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS
1 5	ITEM 1 2 3 4 5 6 7 8 9 10	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A GWL-05		X 11.5 S 1/2" x 1, 1/2" 5/8" 5,	60° TC 5" X .5" 5MALL (4" FU /2" GA /2" GALV ' X 8" C /8" GA	D DISH (I STRAIG DISH CL LL THREA ALV HEX ALV LOC FLAT W GALV TH ALV HEX ALV LOC	ROUND) AE HT BAR ADA AMP HALF AD GALV. B NUT (A325) EK WASHER ASHER (A32 READED RO NUT (A325) EK WASHER	APTOR SOLT 25) DD	2 2 2 4 4 4 8 8 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS
4 5	1 2 3 4 5 6 7 8 9	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A	2"	X 11.5 S 1/2" x 1, 1, 1/2" 5/8" 5, 5/8"	60° TC 5" X .5" 5MALL (4" FU /2" GA /2" GALV ' X 8" C /8" GA	D DISH (I STRAIG DISH CL LL THREA ALV HEX ALV LOC FLAT W GALV TH ALV HEX ALV LOC	ROUND) AE HT BAR AD, AMP HALF AD GALV. B NUT (A325) CK WASHER ASHER (A32 READED RO NUT (A325)	APTOR SOLT 25) DD	2 2 2 4 4 4 8 4 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS
4 5	1 2 3 4 5 6 7 8 9 10 11	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A GWL-05 GWF05A	2"	X 11.5 S 1/2" x 1, 1/2" 5/8" 5,	60° TC 5" X .5" 5MALL (4" FU /2" GA /2" GALV ' X 8" C /8" GA	D DISH (I STRAIG DISH CL LL THREA ALV HEX ALV LOC FLAT W GALV TH ALV HEX ALV LOC FLAT W	ROUND) AE HT BAR ADA AMP HALF AD GALV. B NUT (A325) EK WASHER ASHER (A32 READED RO NUT (A325) EK WASHER	APTOR SOLT 25) DD 25)	2 2 2 4 4 4 8 8 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS
4 5	1 2 3 4 5 6 7 8 9 10 11 These drawing property of A only for the s	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A GWL-05 GWF05A ss and specifications are the proprie specific purpose authorized in writing Andrew Corporation.	2"	X 11.5 S 1/2" x 1, 1/2" 5/8" 5/8" 5/8" ACG	60° TC 5" X .5" 5MALL (4" FU /2" GA /2" GALV ' X 8" C /8" GA GALV	DISH (I STRAIG DISH CL LL THREA ALV HEX ALV LOC FLAT W GALV TH ALV HEX ALV LOC FLAT W	ROUND) AE HT BAR AD AMP HALF AD GALV. B NUT (A325) EK WASHER ASHER (A32 READED RC NUT (A325) EK WASHER ASHER (A32 AD-P60-SC DESCRIPTION	APTOR SOLT 25) DD 25)	2 2 2 4 4 4 8 4 8 8 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS
4 5	ITEM 1 2 3 4 5 6 7 8 9 10 11 These drawing property of A only for the s	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A GWL-05 GWF05A	2"	1/2" x 1/2" x 1, 1/2" x 1, 1/2" 5/8" 5/8" 5/8" ACG	60° TC 5" X .5" 5MALL (4" FU /2" GA /2" GA (2" GA (3" GA (5) 8" GA (5) 8" GA (5) 8" GA	DISH (I STRAIG DISH CL LL THREA ALV HEX ALV LOC FLAT W GALV TH ALV HEX ALV LOC FLAT W	ROUND) AE HT BAR AD, AMP HALF AD GALV. B NUT (A325) CK WASHER ASHER (A32 READED RO NUT (A325) CK WASHER ASHER (A32 AD-P60-S0	APTOR SOLT 25) DD 25)	2 2 2 4 4 4 8 4 8 8 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS
1 5	ITEM 1 2 3 4 5 6 7 8 9 10 11 These drawing property of A only for the s	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A GWL-05 GWF05A Syspecifications are the proprie syspecific purpose authorized in writing Andrew Corporation. RE IN INCHES U.O.S. SS OTHERWISE SPECIFIED: ANGLES	2" stary assed a by by containing the stary assed a by by containing the stary asset as a stary as	X 11.5 S 1/2" x 1, 1/2" 5/8" 5/8" 5/8" ACG	60° TC 5" X .5" 5MALL (4" FU /2" GA /2" GA (2" GA (3" GA (4" GA (5) 8" GA (5) 8" GA (6) 8" GA (6) 8" GA (7) 9" 1 of	DISH (I STRAIG DISH CL LL THREA ALV HEX ALV LOC FLAT W GALV TH ALV HEX ALV LOC FLAT W	ROUND) AE HT BAR AD AMP HALF AD GALV. B NUT (A325) EK WASHER ASHER (A32 READED RO NUT (A325) EK WASHER ASHER (A32 ANT NUMBER AD-P60-SC BESCAPTION ADAPTER CLAMP SET	APTOR SOLT 25) DD 25)	2 2 2 4 4 4 8 4 8 8 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS
5	ITEM 1 2 3 4 5 6 7 8 9 10 11 These drawing property of A only for the s ALL DIMENSIONS AF TOLERANCES UNLES	M60SA MCF SC-P10 12-04-FTB GN04A GWL-04 GWF04A MT-381-8 GN05A GWL-05 GWF05A SMF05A SMF	2"	X 11.5 S 1/2" x 1, 1/2" 5/8" 5/8" 5/8" ACG	60° TC 5" X .5" 5MALL (4" FU /2" GA /2" GA (ALV ' X 8" C /8" GA GALV SHEET 1 OF	DISH (I STRAIG DISH CL LL THREA ALV HEX ALV LOC FLAT W GALV TH ALV HEX ALV LOC FLAT W	ROUND) AE HT BAR AD AMP HALF AD GALV. B NUT (A325) EK WASHER ASHER (A32 READED RC NUT (A325) EK WASHER ASHER (A32 PART NAMBER AD-P60-SC ESCRIPTION ADAPTER CLAMP SET	APTOR SOLT 25) DD 25)	2 2 2 4 4 4 8 8 8 8 8		4.77 LBS 3.08 LBS 1.20 LBS 0.23 LBS 0.08 LBS 0.01 LBS 0.02 LBS 0.64 LBS 0.08 LBS



8 9 10 11

NOTES:

1. ALL METRIC DIMENSIONS ARE IN BRACKETS.