



| ITEM | PART NO. | DESCRIPTION | QTY. | WEIGHT |
|------|----------------|------------------------------------|------|------------|
| 1 | MTC79021416.02 | 14' CENTER CHANNEL | 7 | 154.79 LBS |
| 2 | MTC79021020.01 | 20' SIDE CHANNEL | 2 | 227.29 LBS |
| 3 | MTC7902.03 | CHANNEL ADAPTER ANGLE | 14 | 7.07 LBS |
| 4 | MTC79021414.02 | GRATING SECTION BRACKET 14' CENTER | 1 | 70.94 LBS |
| 5 | GB-05205 | 5/8" X 2" GALV BOLT KIT | 60 | 0.27 LBS |
| 6 | GWF-05 | 5/8" GALV FLAT WASHER | 120 | 0.06 LBS |
| 7 | MTC9170.09 | 24" X 120" BAR GRATING | 14 | 141.45 LBS |
| 8 | GCM03 | GRATING CLIP | 112 | 0.39 LBS |

| REVISIONS | | | | |
|-----------|------|-----------------|-----|----------|
| REV. | ZONE | DESCRIPTION | BY | DATE |
| A | | INITIAL RELEASE | MSM | 04/05/12 |



NOTES:
 1. ALL METRIC DIMENSIONS ARE IN BRACKETS.
 2. GRATING REMOVED FOR CLARITY.

These drawings and specifications are the proprietary property of CommScope Inc. and may be used only for the specific purpose authorized in writing by CommScope Inc.

ALL DIMENSIONS ARE IN INCHES U.O.S.
 TOLERANCES UNLESS OTHERWISE SPECIFIED:
 .X = ± .12 ANGLES ±2°
 .XX = ± .06 FRACTIONS ±1/32
 .XXX = ± .03

REMOVE BURRS AND BREAK EDGES .005

DO NOT SCALE THIS PRINT

| | | |
|-------------------|------------------------|---------------------------------------|
| DRAWN BY: MSM | SHEET: 1 of 1 | PART NUMBER: EQ-P1420-B |
| CHECKED BY: TP | SCALE: NTS | DESCRIPTION: Platform Base 14 x 20 |
| DATE: 04/06/12 | MATERIAL: A36, A568 | DRAWING TYPE: ASSEMBLY DRAWING |
| REVISION: A | FINISH: GALV A123 | Hickory, NC 28602 U.S.A. |
| | WEIGHT: 3761.48 LBS | |