




NOTES:

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 8000027524: REL TO PRODUCTION PER EAO 604932.	27DEC17 LS	JUFYU/YUEMLI
B	ECR 8000027937: UPDATE DRAWING WITH LATEST MODEL.	13JAN18 RY	KEL/X.MEI
C	ECR 8000036581: UPDATE DRAWING WITH LATEST MODEL.	30JUL19 LS	ZHWJ/REX
D	ECR 8000038100: UPDATE DRAWING WITH LATEST MODEL.	07NOV19 PL	PYI/B.SUN



NNH4-65B-R6-V2

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE X ±	2 PLACE .XX ±		
1 PLACE .X ±	ANGLES ±		
FINISH N/A		MATERIAL N/A	
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 & 2, THIRD EDITION (2002)</small>	NAME	DATE	TITLE
	CE LS	12/27/2017	PRODUCT DRAWING
	RW PL1051	11/07/2019	
	RV PY1024	11/07/2019	
	AD BS1055	11/08/2019	
RE BYUAN	11/08/2019		
ECN 8000038100-O			SCALE 1:5
DOCUMENT NO. NNH4-65B-R6-V2-L			
SIZE A2	WORK AREA 23	MODEL	DRAWING
		VERSION 04	STATUS RE
		REVISION E	VERSION 03
		STATUS RE	REVISION E
			SHEET 1 OF 1

DENSITY	g/mm ³
MASS	grams
VOLUME	mm ³
SURFACE AREA	mm ²
HEIGHT	
LENGTH	
WIDTH	